Accessories for Offset Processors

CONVERT.
INTEGRATE.
MONITOR.



CONVERT. INTEGRATE. MONITOR.

There are a wide variety of accessories available for your Glunz & Jensen processor. They add immense value to your processor, helping make your prepress process more efficient and effective.

Accessories for Glunz & Jensen plate processors are divided into four categories:

- Build
- Configure
- Integrate
- Support & Service

Some of the listed accessories are included as standard in specific processor configurations. Not all options are available for all processors see the back page for an overview of standard and optional accessories for each processor. Ask your dealer for further details.

Build

Increase the efficiency of vour processor and keep your prepress room tidy and organised.

Examples: Closed stand

- Cooling unit
- Drip trav
- Hand shower for cleaning
- Developer circuation pump
- Quick fill pump
- Touch screen display

Quick Fill Pump

Fill the developer section with developer without lifting the heavy developer containers by pumping the content of a container on the floor straight into the developer section at 10-12 liters/minute (2.6-3.2 US gallons/minute).



Configure

Reduce chemistry and water usage, waste and expenses with conversion kits and monitoring equipment.

Examples:

- Container level probes
- Developer reconfiguration kit



- Violet Chemfree conversion kit
- Water saving / tap water kit



Unattended processing is supported by container level probes which monitor the levels in containers with replenish, finisher and waste and alerts the operator in case of low/high level in a container.



Integrate

Optimise your workflow in online and offline set-ups with the right accessories to keep plates moving efficiently through your processor.



Online interface for CtP

Safe unattended production. The CtP will only make a new plate if the processor is able to accept it. The Interface kit includes all components for the mechanical AND electrical adaption.



Examples:

- Delivery and feed tables
- Online interface for CtP
- Stackers
- · System conveyor

Support & Service

Operate your processor with added peace-of-mind and convenience.



Connect⁺ Desktop


Add Connect⁺ Desktop for remote support. Monitor, correct settings and diagnose the condition of the processor from a remote computer (via Team Viewer). For example, check and replenish chemistry or monitor waste, water levels, and temperatures.



Examples:

- Connect⁺ Desktop
- Extended parts warranty
- Preventative maintenance kits
- USB memory stick







annual maintenance on your plate processor to keep it in top condition.

Keep your prepress room tidy and organized by hiding containers and other equipment with a closed stand. The easily fitted side panels are easily removed without tools to give full access to the space under the processor.



We recommend using a cooling unit with all processors to maintain a stable developer temperature under all conditions. The included standard cooling unit can be replaced by a high capacity cooling unit if required by special conditions.

> Unattended operation is supported by use of sensors both inside the processor and externally, e.g. container level probes.





For inline configurations, use a system conveyor to connect the processor with the CtP and a stacker to collect plates as they exit the processor.

For offline or manual feed configurations, rest and align plates on the **feed table** and then collect plates on the **delivery table** as they exit the processor.



Developer reconfiguration

enables you change applications on Glunz & Jensen processors and still achieve premium results. Modifications may be required. Easily change the number and type of brushes ask your plate supplier for the optimal configuration.

Simple Violet Chemfree conversion kits are available for Agfa N94-VCF, Fujifilm Pro-V and Kodak Libra VP.



Keep your prepress room tidy and organized with a drip tray to collect fluids which may be accidentally spilled.

InterPlater MD and Kylin can be upgraded with a touch screen display with full functionality.







Stackers provide flexibility in the prepress room. The Compact Stacker (3 sizes) uses gravity to move plates to the integrated tray and can store up to 100 plates.

The PRO Stacker (4 sizes) has a traditional belt drived conveyor and a magnetically coupled trolley for ease of plate transport. Additional trolleys can be bought separately.



Backup you reference configuration, update software, add languages or store data logs and screenshots. This **USB memory stick** is guaranteed to be compatible with our equipment.

Ensure high performance levels with a heavy duty circulation pump with ceramic bearings.





Enjoy peace of mind with 6, 12 or 18 months extended parts warranty.





√ = Standard0 = Optional	InterPlater HDX		Raptor+		InterPlater MD	COU+	Kylin	
MODEL	Thermal	Polymer	Thermal	Polymer	Thermal	Chemfree	Thermal	Polymer
BUILD								
Closed stand	0	0	0	0		$\sqrt{}$		
Cooling unit (integrated)					√		√	V
Cooling unit (standard capacity)	√	√	$\sqrt{}$					
Cooling unit (high capacity)	0	0						
Drip tray	0	0	0	0	0	0	0	0
Hand shower for cleaning	√	√	√	√	0	0	0	0
Heavy duty circulation pump	0	0	0	0	0		0	0
Quick-fill pump / Fill pump	0	0	√	√	0		0	0
Touch screen display	√	$\sqrt{}$	$\sqrt{}$		0		0	0
CONFIGURE								
Container level probe	0	0	$\sqrt{}$	$\sqrt{}$	0	$\sqrt{}$	0	0
Developer reconfiguration	0	0	0	0	0		0	0
Violet Chemfree conversion kit		0		0				0
Water saving kit / Tap water kit	√	$\sqrt{}$	$\sqrt{}$		0 / √		0 / √	0 / √
INTEGRATE								
Compact Stacker	0	0	0	0	0	0	0	0
Delivery table	0	0	0	0	0	0	0	0
Feed table	0	0	0	0	0	0	0	0
Online interface for CtP	0	0	0	0	0	0	0	0
PRO Stacker	0	0	0	0	0	0	0	0
System conveyor	0	0	0	0	0	0	0	0
SUPPORT & SERVICE								
Connect+ Desktop	0	0	0	0	0	0	0	0
Extended parts warranty	0	0	0	0	0	0	0	0
Preventive maintenance kits	0	0	0	0	0	0	0	0
Remote Enabling 1-line display					√		√	√
USB memory stick	0	0	0	0	0	0	0	0



Glunz & Jensen (HQ) Selandia Park 1 4100 Ringsted, Denmark +45 5768 8181 gj@glunz-jensen.com

Glunz & Jensen s.r.o. Kosicka, 50 08001 Prešov, Slovakia +421 51 7563811 gj@glunz-jensen.com

Glunz & Jensen (Americas) 2185 Hwy. 292 Inman, SC 29349, USA +1 864 568 4638 gj-americas@glunz-jensen.com

Stay updated! Follow Glunz & Jensen

